

**Garant**
**Left-hand thread through hole machine tap, TiN, Type: 11/16-24**

**Order data**

Order number	130036 11/16-24
GTIN	4062406041816
Item class	10N

**Description**
**Note:**

Delivery time: 49 calendar days  
 Minimum order quantity: 2 pcs.  
 Special / custom-made product - return not possible  
 Thread type: UNEF-LH  
 Tool material: HSS E  
 Standard: DIN 376  
 Threads per inch: 24  
 Thread  $\varnothing$ : 17.462 mm  
 Overall length L: 125 mm  
 Shank  $\varnothing$  D<sub>s</sub>: 14 mm  
 Shank square  $\square$ : 11 mm  
 Tapping hole  $\varnothing$ : 16.6 mm

**Technical description**

Tool material	HSS E
Overall length L	125 mm
Thread pitch	1.058 mm
Threads per inch	24
Number of clamping slots	3
Thread depth	34.92 mm
Standard	DIN 376

Number of cutting edges Z	3
Shank $\varnothing D_s$	14 mm
Thread $\varnothing$	17.462 mm
Tapping hole $\varnothing$	16.6 mm
Shank square $\square$	11 mm
Thread type	UNEF-LH
Thread size	11/16-24 UNEF LH
Coating	TiN
Flank angle	60°
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap