

Garant**Left-hand thread through hole machine tap, TiN, Type: 7/16-20****Order data**

Order number	130036 7/16-20
GTIN	4062406041533
Item class	10N

Description**Note:**

Delivery time: 49 calendar days

Minimum order quantity: 2 pcs.

Special / custom-made product - return not possible

Thread type: UNF-LH

Tool material: HSS E

Standard: DIN 376

Threads per inch: 20

Thread \varnothing : 11.11 mm

Overall length L: 110 mm

Shank \varnothing D_s: 9 mmShank square \square : 7 mmTapping hole \varnothing : 9.9 mm**Technical description**

Thread \varnothing	11.11 mm
Tapping hole \varnothing	9.9 mm
Number of cutting edges Z	3
Tool material	HSS E
Shank square \square	7 mm
Overall length L	110 mm
Thread pitch	1.27 mm

Shank $\varnothing D_s$	9 mm
Standard	DIN 376
Number of clamping slots	3
Thread depth	33.33 mm
Threads per inch	20
Thread type	UNF-LH
Thread size	7/16-20 UNF LH
Coating	TiN
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap