

Garant
Blind hole machine tap, uncoated, Type: 1.1/2-6

Order data

Order number	130040 1.1/2-6
GTIN	4062406044947
Item class	10N

Description
Note:

Delivery time: 35 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UNC

Tool material: HSS E

Standard: DIN 376

Threads per inch: 6

Thread Ø: 38.1 mm

Overall length L: 200 mm

Shank Ø D_s: 32 mm

Shank square □: 24 mm

Tapping hole Ø: 33.7 mm

Technical description

Tool material	HSS E
Thread depth	95.25 mm
Number of cutting edges Z	4
Threads per inch	6
Shank Ø D _s	32 mm
Number of clamping slots	4
Overall length L	200 mm

Thread pitch	4.233 mm
Standard	DIN 376
Shank square □	24 mm
Thread Ø	38.1 mm
Tapping hole Ø	33.7 mm
Thread type	UNC
Thread size	1.1/2-6 UNC
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap