

Garant**Through hole machine tap, uncoated, Type: 7/16-18****Order data**

Order number	130030 7/16-18
GTIN	4062406034825
Item class	10N

Description**Note:**

Delivery time: 35 calendar days

Minimum order quantity: 2 pcs.

Special / custom-made product - return not possible

Thread type: UNS

Tool material: HSS E

Standard: DIN 376

Threads per inch: 18

Thread \varnothing : 11.11 mm

Overall length L: 110 mm

Shank $\varnothing D_s$: 9 mmShank square \square : 7 mmTapping hole \varnothing : 9.75 mm**Technical description**

Tapping hole \varnothing	9.75 mm
Thread \varnothing	11.11 mm
Shank square \square	7 mm
Shank $\varnothing D_s$	9 mm
Thread pitch	1.411 mm
Tool material	HSS E
Thread depth	33.33 mm

Threads per inch	18
Number of clamping slots	3
Overall length L	110 mm
Standard	DIN 376
Number of cutting edges Z	3
Thread type	UNS
Thread size	7/16-18 UNS
Coating	uncoated
Flank angle	60°
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap