

**Garant**
**Left-hand thread through hole machine tap, uncoated, Type: 1.3/8-8**

**Order data**

Order number	130031 1.3/8-8
GTIN	4062406038076
Item class	10N

**Description**
**Note:**

Delivery time: 35 calendar days  
 Minimum order quantity: 1 pc.  
 Special / custom-made product - return not possible  
 Thread type: UN-LH  
 Tool material: HSS E  
 Standard: DIN 376  
 Threads per inch: 8  
 Thread  $\varnothing$ : 34.925 mm  
 Overall length L: 200 mm  
 Shank  $\varnothing$  D<sub>s</sub>: 28 mm  
 Shank square  $\square$ : 22 mm  
 Tapping hole  $\varnothing$ : 31.9 mm

**Technical description**

Thread depth	69.85 mm
Tool material	HSS E
Thread pitch	3.175 mm
Thread $\varnothing$	34.925 mm
Number of cutting edges Z	4
Shank square $\square$	22 mm
Threads per inch	8
Tapping hole $\varnothing$	31.9 mm

Overall length L	200 mm
Number of clamping slots	4
Standard	DIN 376
Shank $\varnothing D_s$	28 mm
Thread type	UN-LH
Thread size	1.3/8-8 UN LH
Coating	uncoated
Flank angle	60°
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap