

**Garant**
**Through hole machine tap, uncoated, Type: 7/8-18**

**Order data**

Order number	130030 7/8-18
GTIN	4062406035273
Item class	10N

**Description**
**Note:**

Delivery time: 35 calendar days  
 Minimum order quantity: 1 pc.  
 Special / custom-made product - return not possible  
 Thread type: UNS  
 Tool material: HSS E  
 Standard: DIN 376  
 Threads per inch: 18  
 Thread  $\varnothing$ : 22.23 mm  
 Overall length L: 140 mm  
 Shank  $\varnothing$  D<sub>s</sub>: 18 mm  
 Shank square  $\square$ : 14.5 mm  
 Tapping hole  $\varnothing$ : 21 mm

**Technical description**

Standard	DIN 376
Tool material	HSS E
Thread pitch	1.411 mm
Number of clamping slots	3
Overall length L	140 mm
Shank $\varnothing$ D <sub>s</sub>	18 mm
Thread depth	66.69 mm

Number of cutting edges Z	3
Threads per inch	18
Tapping hole Ø	21 mm
Thread Ø	22.23 mm
Shank square □	14.5 mm
Thread type	UNS
Thread size	7/8-18 UNS
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap