

Garant**Left-hand thread through hole machine tap, uncoated, Type: 7/16-16****Order data**

Order number	130031 7/16-16
GTIN	4062406037079
Item class	10N

Description**Note:**

Delivery time: 35 calendar days
Minimum order quantity: 2 pcs.
Special / custom-made product - return not possible
Thread type: UN-LH
Tool material: HSS E
Standard: DIN 376
Threads per inch: 16
Thread \varnothing : 11.11 mm
Overall length L: 110 mm
Shank \varnothing D_s: 9 mm
Shank square \square : 7 mm
Tapping hole \varnothing : 9.576 mm

Technical description

Shank square \square	7 mm
Threads per inch	16
Thread pitch	1.588 mm
Overall length L	110 mm
Tapping hole \varnothing	9.576 mm
Tool material	HSS E
Shank \varnothing D _s	9 mm

Number of cutting edges Z	3
Thread Ø	11.11 mm
Thread depth	33.33 mm
Number of clamping slots	3
Standard	DIN 376
Thread type	UN-LH
Thread size	7/16-16 UN LH
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap