

Garant
Through hole machine tap, uncoated, Type: 1.3/8-12

Order data

Order number	130030 1.3/8-12
GTIN	4062406035815
Item class	10N

Description
Note:

Delivery time: 35 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UNF

Tool material: HSS E

Standard: DIN 376

Threads per inch: 12

Thread Ø: 34.925 mm

Overall length L: 200 mm

Shank Ø D_s: 28 mm

Shank square □: 22 mm

Tapping hole Ø: 32.75 mm

Technical description

Tapping hole Ø	32.75 mm
Thread depth	69.85 mm
Thread Ø	34.925 mm
Shank square □	22 mm
Standard	DIN 376
Overall length L	200 mm
Tool material	HSS E
Thread pitch	2.117 mm

Number of clamping slots	4
Shank $\varnothing D_s$	28 mm
Number of cutting edges Z	4
Threads per inch	12
Thread type	UNF
Thread size	1.3/8-12 UNF
Coating	uncoated
Flank angle	60°
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap