

Garant
Left-hand thread through hole machine tap, uncoated, Type: 1/2-12

Order data

Order number	130031 1/2-12
GTIN	4062406037178
Item class	10N

Description
Note:

Delivery time: 35 calendar days
 Minimum order quantity: 2 pcs.
 Special / custom-made product - return not possible
 Thread type: UNS-LH
 Tool material: HSS E
 Standard: DIN 376
 Threads per inch: 12
 Thread Ø: 12.7 mm
 Overall length L: 110 mm
 Shank Ø D_s: 11 mm
 Shank square □: 9 mm
 Tapping hole Ø: 10.75 mm

Technical description

Thread depth	25.4 mm
Number of clamping slots	3
Thread pitch	2.117 mm
Standard	DIN 376
Threads per inch	12
Number of cutting edges Z	3
Overall length L	110 mm
Shank square □	9 mm

Tapping hole Ø	10.75 mm
Tool material	HSS E
Shank Ø D _s	11 mm
Thread Ø	12.7 mm
Thread type	UNS-LH
Thread size	1/2-12 UNS LH
Coating	uncoated
Flank angle	60°
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap