

Garant**Left-hand thread through hole machine tap, uncoated, Type: 1/4-56****Order data**

Order number	130031 1/4-56
GTIN	4062406036768
Item class	10N

Description**Note:**

Delivery time: 35 calendar days

Minimum order quantity: 3 pcs.

Special / custom-made product - return not possible

Thread type: UNS-LH

Tool material: HSS E

Standard: DIN 371

Threads per inch: 56

Thread Ø: 6.35 mm

Overall length L: 80 mm

Shank Ø D_s: 7 mm

Shank square □: 5.5 mm

Tapping hole Ø: 5.95 mm

Technical description

Tool material	HSS E
Standard	DIN 371
Number of cutting edges Z	3
Shank square □	5.5 mm
Threads per inch	56
Thread Ø	6.35 mm
Thread depth	19.05 mm

Overall length L	80 mm
Thread pitch	0.454 mm
Tapping hole Ø	5.95 mm
Shank Ø D _s	7 mm
Number of clamping slots	3
Thread type	UNS-LH
Thread size	1/4-56 UNS LH
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap