

Garant
Blind hole machine tap, uncoated, Type: 1/2-27

Order data

Order number	130040 1/2-27
GTIN	4062406043827
Item class	10N

Description
Note:

Delivery time: 35 calendar days
 Minimum order quantity: 2 pcs.
 Special / custom-made product - return not possible
 Thread type: UNS
 Tool material: HSS E
 Standard: DIN 376
 Threads per inch: 27
 Thread \varnothing : 12.7 mm
 Overall length L: 110 mm
 Shank \varnothing D_s: 11 mm
 Shank square \square : 9 mm
 Tapping hole \varnothing : 11.85 mm

Technical description

Thread \varnothing	12.7 mm
Overall length L	110 mm
Tapping hole \varnothing	11.85 mm
Shank square \square	9 mm
Tool material	HSS E
Thread depth	31.75 mm
Shank \varnothing D _s	11 mm

Thread pitch	0.94 mm
Threads per inch	27
Number of cutting edges Z	3
Standard	DIN 376
Number of clamping slots	3
Thread type	UNS
Thread size	1/2-27 UNS
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap