

Garant
Left-hand thread through hole machine tap, uncoated, Type: 7/16-20

Order data

Order number	130031 7/16-20
GTIN	4062406037055
Item class	10N

Description
Note:

Delivery time: 35 calendar days
 Minimum order quantity: 2 pcs.
 Special / custom-made product - return not possible
 Thread type: UNF-LH
 Tool material: HSS E
 Standard: DIN 376
 Threads per inch: 20
 Thread \varnothing : 11.11 mm
 Overall length L: 110 mm
 Shank \varnothing D_s: 9 mm
 Shank square \square : 7 mm
 Tapping hole \varnothing : 9.9 mm

Technical description

Tool material	HSS E
Standard	DIN 376
Number of cutting edges Z	3
Threads per inch	20
Thread depth	33.33 mm
Overall length L	110 mm
Shank \varnothing D _s	9 mm

Thread Ø	11.11 mm
Thread pitch	1.27 mm
Tapping hole Ø	9.9 mm
Shank square □	7 mm
Number of clamping slots	3
Thread type	UNF-LH
Thread size	7/16-20 UNF LH
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap