

Garant**Through hole machine tap, uncoated, Type: 1.7/16-12****Order data**

Order number	130030 1.7/16-12
GTIN	4062406035884
Item class	10N

Description**Note:**

Delivery time: 35 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UN

Tool material: HSS E

Standard: DIN 376

Threads per inch: 12

Thread \varnothing : 36.512 mm

Overall length L: 200 mm

Shank \varnothing D_s: 28 mmShank square \square : 22 mmTapping hole \varnothing : 34.5 mm**Technical description**

Shank \varnothing D _s	28 mm
Shank square \square	22 mm
Tapping hole \varnothing	34.5 mm
Thread pitch	2.117 mm
Overall length L	200 mm
Thread depth	73 mm
Threads per inch	12

Tool material	HSS E
Thread Ø	36.512 mm
Standard	DIN 376
Number of clamping slots	4
Number of cutting edges Z	4
Thread type	UN
Thread size	1.7/16-12 UN
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap