

**Garant****Left-hand thread through hole machine tap, uncoated, Type: 11/16-12****Order data**

Order number	130031 11/16-12
GTIN	4062406037369
Item class	10N

**Description****Note:**

Delivery time: 35 calendar days

Minimum order quantity: 2 pcs.

Special / custom-made product - return not possible

Thread type: UN-LH

Tool material: HSS E

Standard: DIN 376

Threads per inch: 12

Thread  $\varnothing$ : 17.462 mm

Overall length L: 125 mm

Shank  $\varnothing$  D<sub>s</sub>: 14 mm

Shank square □: 11 mm

Tapping hole  $\varnothing$ : 15.5 mm**Technical description**

Number of clamping slots	3
Thread pitch	2.117 mm
Threads per inch	12
Number of cutting edges Z	3
Tool material	HSS E
Shank $\varnothing$ D <sub>s</sub>	14 mm
Tapping hole $\varnothing$	15.5 mm

Shank square □	11 mm
Thread Ø	17.462 mm
Thread depth	34.92 mm
Standard	DIN 376
Overall length L	125 mm
Thread type	UN-LH
Thread size	11/16-12 UN LH
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap