

Garant**Through hole machine tap, uncoated, Type: 11/16-12****Order data**

Order number	130030 11/16-12
GTIN	4062406035129
Item class	10N

Description**Note:**

Delivery time: 35 calendar days
Minimum order quantity: 2 pcs.
Special / custom-made product - return not possible
Thread type: UN
Tool material: HSS E
Standard: DIN 376
Threads per inch: 12
Thread \varnothing : 17.462 mm
Overall length L: 125 mm
Shank \varnothing D_s: 14 mm
Shank square \square : 11 mm
Tapping hole \varnothing : 15.5 mm

Technical description

Tool material	HSS E
Number of cutting edges Z	3
Shank square \square	11 mm
Overall length L	125 mm
Tapping hole \varnothing	15.5 mm
Thread \varnothing	17.462 mm
Standard	DIN 376

Threads per inch	12
Shank $\varnothing D_s$	14 mm
Number of clamping slots	3
Thread depth	34.92 mm
Thread pitch	2.117 mm
Thread type	UN
Thread size	11/16-12 UN
Coating	uncoated
Flank angle	60°
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap