

Garant**Through hole machine tap, uncoated, Type: 3/4-10****Order data**

Order number	130030 3/4-10
GTIN	4062406035204
Item class	10N

Description**Note:**

Delivery time: 35 calendar days

Minimum order quantity: 2 pcs.

Special / custom-made product - return not possible

Thread type: UNC

Tool material: HSS E

Standard: DIN 376

Threads per inch: 10

Thread \varnothing : 19.05 mm

Overall length L: 125 mm

Shank \varnothing D_s: 14 mmShank square \square : 11 mmTapping hole \varnothing : 16.46 mm**Technical description**

Threads per inch	10
Tapping hole \varnothing	16.46 mm
Shank \varnothing D _s	14 mm
Number of cutting edges Z	3
Overall length L	125 mm
Standard	DIN 376
Thread \varnothing	19.05 mm

Shank square <input type="checkbox"/>	11 mm
Tool material	HSS E
Thread depth	57.15 mm
Number of clamping slots	3
Thread pitch	2.54 mm
Thread type	UNC
Thread size	3/4-10 UNC
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap