

Garant**Left-hand thread through hole machine tap, uncoated, Type: 7/16-24****Order data**

Order number	130031 7/16-24
GTIN	4062406037048
Item class	10N

Description**Note:**

Delivery time: 35 calendar days
Minimum order quantity: 2 pcs.
Special / custom-made product - return not possible
Thread type: UNS-LH
Tool material: HSS E
Standard: DIN 376
Threads per inch: 24
Thread \varnothing : 11.11 mm
Overall length L: 110 mm
Shank \varnothing D_s: 9 mm
Shank square \square : 7 mm
Tapping hole \varnothing : 10.1 mm

Technical description

Tapping hole \varnothing	10.1 mm
Number of cutting edges Z	3
Shank square \square	7 mm
Number of clamping slots	3
Thread depth	33.33 mm
Tool material	HSS E
Threads per inch	24

Overall length L	110 mm
Thread pitch	1.058 mm
Thread Ø	11.11 mm
Standard	DIN 376
Shank Ø D _s	9 mm
Thread type	UNS-LH
Thread size	7/16-24 UNS LH
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap