

Garant
Left-hand thread through hole machine tap, uncoated, Type: 7/8-24

Order data

Order number	130031 7/8-24
GTIN	4062406037499
Item class	10N

Description
Note:

Delivery time: 35 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UNS-LH

Tool material: HSS E

Standard: DIN 376

Threads per inch: 24

Thread Ø: 22.23 mm

Overall length L: 140 mm

Shank Ø D_s: 18 mm

Shank square □: 14.5 mm

Tapping hole Ø: 21.2 mm

Technical description

Standard	DIN 376
Tool material	HSS E
Thread Ø	22.23 mm
Shank square □	14.5 mm
Number of clamping slots	3
Number of cutting edges Z	3
Thread depth	66.69 mm

Overall length L	140 mm
Thread pitch	1.058 mm
Threads per inch	24
Tapping hole Ø	21.2 mm
Shank Ø D _s	18 mm
Thread type	UNS-LH
Thread size	7/8-24 UNS LH
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap