

Garant
Left-hand thread through hole machine tap, uncoated, Type: 3/4-10

Order data

Order number	130031 3/4-10
GTIN	4062406037444
Item class	10N

Description
Note:

Delivery time: 35 calendar days
 Minimum order quantity: 2 pcs.
 Special / custom-made product - return not possible
 Thread type: UNC-LH
 Tool material: HSS E
 Standard: DIN 376
 Threads per inch: 10
 Thread \varnothing : 19.05 mm
 Overall length L: 125 mm
 Shank \varnothing D_s: 14 mm
 Shank square □: 11 mm
 Tapping hole \varnothing : 16.46 mm

Technical description

Number of clamping slots	3
Tapping hole \varnothing	16.46 mm
Thread \varnothing	19.05 mm
Tool material	HSS E
Overall length L	125 mm
Number of cutting edges Z	3
Shank \varnothing D _s	14 mm

Shank square <input type="checkbox"/>	11 mm
Standard	DIN 376
Thread depth	57.15 mm
Thread pitch	2.54 mm
Threads per inch	10
Thread type	UNC-LH
Thread size	3/4-10 UNC LH
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap