

Garant
Blind hole machine tap, uncoated, Type: 1.1/2-12

Order data

| | |
|--------------|-----------------|
| Order number | 130040 1.1/2-12 |
| GTIN | 4062406044916 |
| Item class | 10N |

Description
Note:

Delivery time: 35 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UNF

Tool material: HSS E

Standard: DIN 376

Threads per inch: 12

Thread Ø: 38.1 mm

Overall length L: 200 mm

Shank Ø D_s: 32 mm

Shank square □: 24 mm

Tapping hole Ø: 36 mm

Technical description

| | |
|--------------------------|----------|
| Thread Ø | 38.1 mm |
| Standard | DIN 376 |
| Thread depth | 95.25 mm |
| Number of clamping slots | 4 |
| Tool material | HSS E |
| Shank square □ | 24 mm |
| Thread pitch | 2.117 mm |

| | |
|----------------------------------|--|
| Overall length L | 200 mm |
| Shank $\varnothing D_s$ | 32 mm |
| Number of cutting edges Z | 4 |
| Threads per inch | 12 |
| Tapping hole \varnothing | 36 mm |
| Thread type | UNF |
| Thread size | 1.1/2-12 UNF |
| Coating | uncoated |
| Flank angle | 60° |
| Thread standard | ASME B1.1 |
| Tolerance class | 1B |
| Tolerance class | 2B +0.20 |
| Tolerance class | 2B +0.10 |
| Tolerance class | 3B |
| Tolerance class | 2B |
| Tolerance class | 2B +0.05 |
| Taper lead form | C |
| Shank | Plain shank with h9 |
| Through-coolant | no |
| Application for type of drilling | up to 2xD for blind holes |
| Cutting direction | right-hand |
| Type of threading tool | Machine tap for conventional machining |
| Colour ring | without |
| Type of product | Tap |