

Garant
Through hole machine tap, uncoated, Type: 3/4-12

Order data

Order number	130030 3/4-12
GTIN	4062406035198
Item class	10N

Description
Note:

Delivery time: 35 calendar days
 Minimum order quantity: 2 pcs.
 Special / custom-made product - return not possible
 Thread type: UN
 Tool material: HSS E
 Standard: DIN 376
 Threads per inch: 12
 Thread \varnothing : 19.05 mm
 Overall length L: 125 mm
 Shank \varnothing D_s: 14 mm
 Shank square \square : 11 mm
 Tapping hole \varnothing : 17 mm

Technical description

Tool material	HSS E
Overall length L	125 mm
Shank square \square	11 mm
Threads per inch	12
Number of clamping slots	3
Shank \varnothing D _s	14 mm
Thread \varnothing	19.05 mm
Standard	DIN 376

Thread pitch	2.117 mm
Thread depth	38.1 mm
Tapping hole Ø	17 mm
Number of cutting edges Z	3
Thread type	UN
Thread size	3/4-12 UN
Coating	uncoated
Flank angle	60°
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap