

Garant**Left-hand thread through hole machine tap, uncoated, Type: 9/16-12****Order data**

Order number	130031 9/16-12
GTIN	4062406037246
Item class	10N

Description**Note:**

Delivery time: 35 calendar days

Minimum order quantity: 2 pcs.

Special / custom-made product - return not possible

Thread type: UNC-LH

Tool material: HSS E

Standard: DIN 376

Threads per inch: 12

Thread \varnothing : 14.29 mm

Overall length L: 110 mm

Shank \varnothing D_s: 11 mmShank square \square : 9 mmTapping hole \varnothing : 12.15 mm**Technical description**

Number of clamping slots	3
Tapping hole \varnothing	12.15 mm
Standard	DIN 376
Number of cutting edges Z	3
Shank square \square	9 mm
Shank \varnothing D _s	11 mm
Threads per inch	12

Thread pitch	2.117 mm
Thread depth	57.16 mm
Overall length L	110 mm
Thread Ø	14.29 mm
Tool material	HSS E
Thread type	UNC-LH
Thread size	9/16-12 UNC LH
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap