

Garant
Left-hand thread through hole machine tap, uncoated, Type: NO.5-40

Order data

Order number	130031 NO.5-40
GTIN	4062406036577
Item class	10N

Description
Note:

Delivery time: 35 calendar days

Minimum order quantity: 3 pcs.

Special / custom-made product - return not possible

Thread type: UNC-LH

Tool material: HSS E

Standard: DIN 371

Threads per inch: 40

Thread \varnothing : 3.18 mm

Overall length L: 56 mm

Shank \varnothing D_s: 3.5 mm

Shank square \square : 2.7 mm

Tapping hole \varnothing : 2.59 mm

Technical description

Thread depth	9.54 mm
Number of cutting edges Z	3
Shank \varnothing D _s	3.5 mm
Tapping hole \varnothing	2.59 mm
Tool material	HSS E
Thread pitch	0.635 mm
Standard	DIN 371

Threads per inch	40
Overall length L	56 mm
Shank square □	2.7 mm
Thread Ø	3.18 mm
Number of clamping slots	3
Thread type	UNC-LH
Thread size	5-40 UNC LH
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap