

**Garant**
**Blind hole machine tap, uncoated, Type: 2-8**

**Order data**

Order number	130040 2-8
GTIN	4062406045425
Item class	10N

**Description**
**Note:**

Delivery time: 35 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UN

Tool material: HSS E

Standard: DIN 376

Threads per inch: 8

Thread  $\varnothing$ : 50.8 mm

Overall length L: 250 mm

Shank  $\varnothing$  D<sub>s</sub>: 40 mm

Shank square  $\square$ : 32 mm

Tapping hole  $\varnothing$ : 47.8 mm

**Technical description**

Number of clamping slots	4
Thread pitch	3.175 mm
Thread depth	127 mm
Tapping hole $\varnothing$	47.8 mm
Shank $\varnothing$ D <sub>s</sub>	40 mm
Threads per inch	8
Standard	DIN 376

Thread Ø	50.8 mm
Overall length L	250 mm
Shank square □	32 mm
Number of cutting edges Z	4
Tool material	HSS E
Thread type	UN
Thread size	2-8 UN
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap