

Garant**Left-hand thread through hole machine tap, uncoated, Type: NO.8-36****Order data**

Order number	130031 NO.8-36
GTIN	4062406036607
Item class	10N

Description**Note:**

Delivery time: 35 calendar days

Minimum order quantity: 3 pcs.

Special / custom-made product - return not possible

Thread type: UNF-LH

Tool material: HSS E

Standard: DIN 371

Threads per inch: 36

Thread Ø: 4.17 mm

Overall length L: 63 mm

Shank Ø D_s: 4.5 mm

Shank square □: 3.4 mm

Tapping hole Ø: 3.5 mm

Technical description

Thread depth	12.51 mm
Shank square □	3.4 mm
Overall length L	63 mm
Threads per inch	36
Number of clamping slots	3
Thread pitch	0.706 mm
Tapping hole Ø	3.5 mm

Standard	DIN 371
Thread Ø	4.17 mm
Number of cutting edges Z	3
Shank Ø D _s	4.5 mm
Tool material	HSS E
Thread type	UNF-LH
Thread size	8-36 UNF LH
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap