

Garant
Blind hole machine tap, uncoated, Type: NO.8-32

Order data

Order number	130040 NO.8-32
GTIN	4062406043339
Item class	10N

Description
Note:

Delivery time: 35 calendar days
 Minimum order quantity: 3 pcs.
 Special / custom-made product - return not possible
 Thread type: UNC
 Tool material: HSS E
 Standard: DIN 371
 Threads per inch: 32
 Thread \varnothing : 4.166 mm
 Overall length L: 63 mm
 Shank \varnothing D_s : 4.5 mm
 Shank square \square : 3.4 mm
 Tapping hole \varnothing : 3.42 mm

Technical description

Thread \varnothing	4.166 mm
Thread pitch	0.794 mm
Threads per inch	32
Shank \varnothing D_s	4.5 mm
Tool material	HSS E
Shank square \square	3.4 mm
Number of clamping slots	3

Overall length L	63 mm
Tapping hole Ø	3.42 mm
Thread depth	10.4 mm
Number of cutting edges Z	3
Standard	DIN 371
Thread type	UNC
Thread size	8-32 UNC
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap