

**Garant****Through hole machine tap, TiN, Type: 7/16-28****Order data**

Order number	130035 7/16-28
GTIN	4062406039264
Item class	10N

**Description****Note:**

Delivery time: 49 calendar days

Minimum order quantity: 2 pcs.

Special / custom-made product - return not possible

Thread type: UNEF

Tool material: HSS E

Standard: DIN 376

Threads per inch: 28

Thread  $\varnothing$ : 11.11 mm

Overall length L: 110 mm

Shank  $\varnothing$  D<sub>s</sub>: 9 mmShank square  $\square$ : 7 mmTapping hole  $\varnothing$ : 10.35 mm**Technical description**

Number of clamping slots	3
Overall length L	110 mm
Thread $\varnothing$	11.11 mm
Tapping hole $\varnothing$	10.35 mm
Shank $\varnothing$ D <sub>s</sub>	9 mm
Number of cutting edges Z	3
Tool material	HSS E

Standard	DIN 376
Threads per inch	28
Thread pitch	0.907 mm
Shank square □	7 mm
Thread depth	33.33 mm
Thread type	UNEF
Thread size	7/16-28 UNEF
Coating	TiN
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap