

Garant
Left-hand thread through hole machine tap, uncoated, Type: 2-8

Order data

Order number	130031 2-8
GTIN	4062406038700
Item class	10N

Description
Note:

Delivery time: 35 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UN-LH

Tool material: HSS E

Standard: DIN 376

Threads per inch: 8

Thread \varnothing : 50.8 mm

Overall length L: 250 mm

Shank \varnothing D_s: 40 mm

Shank square \square : 32 mm

Tapping hole \varnothing : 47.8 mm

Technical description

Number of cutting edges Z	4
Shank \varnothing D _s	40 mm
Thread depth	101.6 mm
Standard	DIN 376
Tool material	HSS E
Shank square \square	32 mm
Overall length L	250 mm
Tapping hole \varnothing	47.8 mm

Thread pitch	3.175 mm
Threads per inch	8
Number of clamping slots	4
Thread Ø	50.8 mm
Thread type	UN-LH
Thread size	2-8 UN LH
Coating	uncoated
Flank angle	60°
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap