

Garant**Blind hole machine tap, uncoated, Type: 2-20****Order data**

Order number	130040 2-20
GTIN	4062406045364
Item class	10N

Description**Note:**

Delivery time: 35 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UN

Tool material: HSS E

Standard: DIN 376

Threads per inch: 20

Thread \varnothing : 50.8 mm

Overall length L: 250 mm

Shank \varnothing D_s: 40 mmShank square \square : 32 mmTapping hole \varnothing : 49.58 mm**Technical description**

Thread \varnothing	50.8 mm
Thread pitch	1.27 mm
Overall length L	250 mm
Number of cutting edges Z	4
Standard	DIN 376
Tapping hole \varnothing	49.58 mm
Thread depth	127 mm

Tool material	HSS E
Shank $\varnothing D_s$	40 mm
Shank square \square	32 mm
Number of clamping slots	4
Threads per inch	20
Thread type	UN
Thread size	2-20 UN
Coating	uncoated
Flank angle	60°
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2xD for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap