

**Garant**
**Left-hand thread through hole machine tap, TiN, Type: 1-18**

**Order data**

Order number	130036 1-18
GTIN	4062406042110
Item class	10N

**Description**
**Note:**

Delivery time: 49 calendar days  
 Minimum order quantity: 1 pc.  
 Special / custom-made product - return not possible  
 Thread type: UNS-LH  
 Tool material: HSS E  
 Standard: DIN 376  
 Threads per inch: 18  
 Thread  $\varnothing$ : 25.4 mm  
 Overall length L: 160 mm  
 Shank  $\varnothing$  D<sub>s</sub>: 20 mm  
 Shank square  $\square$ : 16 mm  
 Tapping hole  $\varnothing$ : 24.25 mm

**Technical description**

Number of cutting edges Z	4
Shank square $\square$	16 mm
Tapping hole $\varnothing$	24.25 mm
Shank $\varnothing$ D <sub>s</sub>	20 mm
Number of clamping slots	4
Tool material	HSS E
Overall length L	160 mm

Standard	DIN 376
Thread depth	76.2 mm
Thread pitch	1.411 mm
Thread Ø	25.4 mm
Threads per inch	18
Thread type	UNS-LH
Thread size	1-18 UNS LH
Coating	TiN
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap