

Garant
Through hole machine tap, TiN, Type: 9/16-14

Order data

Order number	130035 9/16-14
GTIN	4062406039479
Item class	10N

Description
Note:

Delivery time: 49 calendar days

Minimum order quantity: 2 pcs.

Special / custom-made product - return not possible

Thread type: UNS

Tool material: HSS E

Standard: DIN 376

Threads per inch: 14

Thread Ø: 14.29 mm

Overall length L: 110 mm

Shank Ø D_s: 11 mm

Shank square □: 9 mm

Tapping hole Ø: 12.6 mm

Technical description

Shank square □	9 mm
Number of clamping slots	3
Thread pitch	1.814 mm
Threads per inch	14
Thread Ø	14.29 mm
Standard	DIN 376
Tool material	HSS E

Number of cutting edges Z	3
Thread depth	57.16 mm
Shank $\varnothing D_s$	11 mm
Tapping hole \varnothing	12.6 mm
Overall length L	110 mm
Thread type	UNS
Thread size	9/16-14 UNS
Coating	TiN
Flank angle	60°
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap