

Garant
Through hole machine tap, TiN, Type: 3/4-12

Order data

| | |
|--------------|---------------|
| Order number | 130035 3/4-12 |
| GTIN | 4062406039677 |
| Item class | 10N |

Description
Note:

Delivery time: 49 calendar days

Minimum order quantity: 2 pcs.

Special / custom-made product - return not possible

Thread type: UN

Tool material: HSS E

Standard: DIN 376

Threads per inch: 12

Thread Ø: 19.05 mm

Overall length L: 125 mm

Shank Ø D_s: 14 mm

Shank square □: 11 mm

Tapping hole Ø: 17 mm

Technical description

| | |
|------------------------|----------|
| Thread pitch | 2.117 mm |
| Thread depth | 38.1 mm |
| Overall length L | 125 mm |
| Threads per inch | 12 |
| Shank Ø D _s | 14 mm |
| Shank square □ | 11 mm |
| Standard | DIN 376 |
| Tool material | HSS E |

| | |
|----------------------------------|--|
| Number of cutting edges Z | 3 |
| Tapping hole Ø | 17 mm |
| Number of clamping slots | 3 |
| Thread Ø | 19.05 mm |
| Thread type | UN |
| Thread size | 3/4-12 UN |
| Coating | TiN |
| Flank angle | 60° |
| Thread standard | ASME B1.1 |
| Tolerance class | 1B |
| Tolerance class | 2B +0.20 |
| Tolerance class | 2B +0.10 |
| Tolerance class | 3B |
| Tolerance class | 2B |
| Tolerance class | 2B +0.05 |
| Taper lead form | B |
| Shank | Plain shank with h9 |
| Through-coolant | no |
| Application for type of drilling | up to 3×D for through holes |
| Cutting direction | right-hand |
| Type of threading tool | Machine tap for conventional machining |
| Colour ring | without |
| Type of product | Tap |