

Garant
Left-hand thread through hole machine tap, uncoated, Type: 1.7/8-10

Order data

Order number	130031 1.7/8-10
GTIN	4062406038588
Item class	10N

Description
Note:

Delivery time: 35 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UNS-LH

Tool material: HSS E

Standard: DIN 376

Threads per inch: 10

Thread \varnothing : 47.625 mm

Overall length L: 250 mm

Shank \varnothing D_s: 36 mm

Shank square □: 29 mm

Tapping hole \varnothing : 45.3 mm

Technical description

Overall length L	250 mm
Standard	DIN 376
Tapping hole \varnothing	45.3 mm
Shank \varnothing D _s	36 mm
Number of clamping slots	4
Threads per inch	10
Thread pitch	2.54 mm
Thread depth	95.25 mm

Shank square <input type="checkbox"/>	29 mm
Tool material	HSS E
Thread \varnothing	47.625 mm
Number of cutting edges Z	4
Thread type	UNS-LH
Thread size	1.7/8-10 UNS LH
Coating	uncoated
Flank angle	60°
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap