

**Garant**
**Through hole machine tap, TiN, Type: NO.2-56**

**Order data**

Order number	130035 NO.2-56
GTIN	4062406038755
Item class	10N

**Description**
**Note:**

Delivery time: 91 calendar days  
 Minimum order quantity: 25 pcs.  
 Special / custom-made product - return not possible  
 Thread type: UNC  
 Tool material: HSS E  
 Standard: DIN 371  
 Threads per inch: 56  
 Thread  $\varnothing$ : 2.18 mm  
 Overall length L: 45 mm  
 Shank  $\varnothing$  D<sub>s</sub>: 2.8 mm  
 Shank square  $\square$ : 2.1 mm  
 Tapping hole  $\varnothing$ : 1.78 mm

**Technical description**

Thread $\varnothing$	2.18 mm
Number of clamping slots	3
Standard	DIN 371
Thread pitch	0.454 mm
Thread depth	6.54 mm
Shank square $\square$	2.1 mm
Number of cutting edges Z	3

Threads per inch	56
Tapping hole Ø	1.78 mm
Overall length L	45 mm
Tool material	HSS E
Shank Ø D <sub>s</sub>	2.8 mm
Thread type	UNC
Thread size	2-56 UNC
Coating	TiN
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap