

Garant
Through hole machine tap, TiN, Type: 3/8-24

Order data

Order number	130035 3/8-24
GTIN	4062406039219
Item class	10N

Description
Note:

Delivery time: 49 calendar days

Minimum order quantity: 3 pcs.

Special / custom-made product - return not possible

Thread type: UNF

Tool material: HSS E

Standard: DIN 371

Threads per inch: 24

Thread Ø: 9.525 mm

Overall length L: 100 mm

Shank Ø D_s: 10 mm

Shank square □: 8 mm

Tapping hole Ø: 8.5 mm

Technical description

Threads per inch	24
Number of cutting edges Z	3
Number of clamping slots	3
Tapping hole Ø	8.5 mm
Standard	DIN 371
Thread Ø	9.525 mm
Shank Ø D _s	10 mm

Shank square <input type="checkbox"/>	8 mm
Thread pitch	1.058 mm
Thread depth	28.59 mm
Overall length L	100 mm
Tool material	HSS E
Thread type	UNF
Thread size	3/8-24 UNF
Coating	TiN
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap