

Garant
Left-hand thread blind hole machine tap, uncoated, Type: 1.5/8-12

Order data

Order number	130041 1.5/8-12
GTIN	4062406047290
Item class	10N

Description
Note:

Delivery time: 35 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UN-LH

Tool material: HSS E

Standard: DIN 376

Threads per inch: 12

Thread \varnothing : 41.275 mm

Overall length L: 200 mm

Shank \varnothing D_s: 32 mm

Shank square \square : 24 mm

Tapping hole \varnothing : 39.3 mm

Technical description

Shank \varnothing D _s	32 mm
Thread \varnothing	41.275 mm
Number of cutting edges Z	4
Number of clamping slots	4
Overall length L	200 mm
Thread depth	103.19 mm
Shank square \square	24 mm

Standard	DIN 376
Tool material	HSS E
Threads per inch	12
Thread pitch	2.117 mm
Tapping hole Ø	39.3 mm
Thread type	UN-LH
Thread size	1.5/8-12 UN LH
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap