

Garant**Left-hand thread blind hole machine tap, uncoated, Type: 11/16-16****Order data**

Order number	130041 11/16-16
GTIN	4062406046316
Item class	10N

Description**Note:**

Delivery time: 35 calendar days

Minimum order quantity: 2 pcs.

Special / custom-made product - return not possible

Thread type: UN-LH

Tool material: HSS E

Standard: DIN 376

Threads per inch: 16

Thread \varnothing : 17.462 mm

Overall length L: 125 mm

Shank \varnothing D_s: 14 mmShank square \square : 11 mmTapping hole \varnothing : 16 mm**Technical description**

Standard	DIN 376
Shank \varnothing D _s	14 mm
Number of cutting edges Z	4
Overall length L	125 mm
Thread pitch	1.588 mm
Threads per inch	16
Thread depth	43.7 mm

Tapping hole Ø	16 mm
Number of clamping slots	4
Thread Ø	17.462 mm
Tool material	HSS E
Shank square □	11 mm
Thread type	UN-LH
Thread size	11/16-16 UN LH
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap