

Garant**Left-hand thread blind hole machine tap, uncoated, Type: 11/16-24****Order data**

Order number	130041 11/16-24
GTIN	4062406046293
Item class	10N

Description**Note:**

Delivery time: 35 calendar days
Minimum order quantity: 2 pcs.
Special / custom-made product - return not possible
Thread type: UNEF-LH
Tool material: HSS E
Standard: DIN 376
Threads per inch: 24
Thread \varnothing : 17.462 mm
Overall length L: 125 mm
Shank \varnothing D_s: 14 mm
Shank square \square : 11 mm
Tapping hole \varnothing : 16.6 mm

Technical description

Shank square \square	11 mm
Number of clamping slots	4
Tapping hole \varnothing	16.6 mm
Thread pitch	1.058 mm
Thread depth	43.7 mm
Number of cutting edges Z	4
Threads per inch	24

Tool material	HSS E
Overall length L	125 mm
Thread Ø	17.462 mm
Standard	DIN 376
Shank Ø D _s	14 mm
Thread type	UNEF-LH
Thread size	11/16-24 UNEF LH
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap