

**Garant**
**Through hole machine tap, TiN, Type: 7/16-16**

**Order data**

Order number	130035 7/16-16
GTIN	4062406039318
Item class	10N

**Description**
**Note:**

Delivery time: 49 calendar days  
 Minimum order quantity: 2 pcs.  
 Special / custom-made product - return not possible  
 Thread type: UN  
 Tool material: HSS E  
 Standard: DIN 376  
 Threads per inch: 16  
 Thread  $\varnothing$ : 11.11 mm  
 Overall length L: 110 mm  
 Shank  $\varnothing$  D<sub>s</sub>: 9 mm  
 Shank square  $\square$ : 7 mm  
 Tapping hole  $\varnothing$ : 9.576 mm

**Technical description**

Shank square $\square$	7 mm
Thread depth	33.33 mm
Number of clamping slots	3
Threads per inch	16
Thread $\varnothing$	11.11 mm
Standard	DIN 376
Thread pitch	1.588 mm

Overall length L	110 mm
Tapping hole Ø	9.576 mm
Number of cutting edges Z	3
Shank Ø D <sub>s</sub>	9 mm
Tool material	HSS E
Thread type	UN
Thread size	7/16-16 UN
Coating	TiN
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap