

Garant
Left-hand thread through hole machine tap, uncoated, Type: 2-16

Order data

Order number	130031 2-16
GTIN	4062406038663
Item class	10N

Description
Note:

Delivery time: 35 calendar days
 Minimum order quantity: 1 pc.
 Special / custom-made product - return not possible
 Thread type: UN-LH
 Tool material: HSS E
 Standard: DIN 376
 Threads per inch: 16
 Thread \varnothing : 50.8 mm
 Overall length L: 250 mm
 Shank \varnothing D_s: 40 mm
 Shank square \square : 32 mm
 Tapping hole \varnothing : 49.3 mm

Technical description

Threads per inch	16
Thread pitch	1.588 mm
Thread \varnothing	50.8 mm
Shank \varnothing D _s	40 mm
Shank square \square	32 mm
Number of clamping slots	4
Thread depth	101.6 mm
Number of cutting edges Z	4

Standard	DIN 376
Tapping hole Ø	49.3 mm
Overall length L	250 mm
Tool material	HSS E
Thread type	UN-LH
Thread size	2-16 UN LH
Coating	uncoated
Flank angle	60°
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap