

Garant**Blind hole machine tap, TiN, Type: 1.1/16-8****Order data**

Order number	130045 1.1/16-8
GTIN	4062406048938
Item class	10N

Description**Note:**

Delivery time: 49 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UN

Tool material: HSS E

Standard: DIN 376

Threads per inch: 8

Thread \varnothing : 26.99 mm

Overall length L: 160 mm

Shank \varnothing D_s: 20 mmShank square \square : 16 mmTapping hole \varnothing : 24 mm**Technical description**

Threads per inch	8
Standard	DIN 376
Shank \varnothing D _s	20 mm
Tapping hole \varnothing	24 mm
Number of cutting edges Z	4
Thread \varnothing	26.99 mm
Overall length L	160 mm

Thread pitch	3.175 mm
Tool material	HSS E
Number of clamping slots	4
Thread depth	67.5 mm
Shank square □	16 mm
Thread type	UN
Thread size	1.1/16-8 UN
Coating	TiN
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap