

Garant
Left-hand thread blind hole machine tap, uncoated, Type: 9/16-16

Order data

Order number	130041 9/16-16
GTIN	4062406046187
Item class	10N

Description
Note:

Delivery time: 35 calendar days
 Minimum order quantity: 2 pcs.
 Special / custom-made product - return not possible
 Thread type: UN-LH
 Tool material: HSS E
 Standard: DIN 376
 Threads per inch: 16
 Thread \varnothing : 14.288 mm
 Overall length L: 110 mm
 Shank \varnothing D_s: 11 mm
 Shank square \square : 9 mm
 Tapping hole \varnothing : 12.8 mm

Technical description

Number of cutting edges Z	3
Thread \varnothing	14.288 mm
Shank square \square	9 mm
Number of clamping slots	3
Tapping hole \varnothing	12.8 mm
Tool material	HSS E
Threads per inch	16

Overall length L	110 mm
Thread depth	35.72 mm
Standard	DIN 376
Shank $\varnothing D_s$	11 mm
Thread pitch	1.588 mm
Thread type	UN-LH
Thread size	9/16-16 UN LH
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2xD for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap