

Garant
Blind hole machine tap, TiN, Type: 1.1/2-14

Order data

Order number	130045 1.1/2-14
GTIN	4062406049386
Item class	10N

Description
Note:

Delivery time: 49 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UNS

Tool material: HSS E

Standard: DIN 376

Threads per inch: 14

Thread Ø: 38.1 mm

Overall length L: 200 mm

Shank Ø D_s: 32 mm

Shank square □: 24 mm

Tapping hole Ø: 36.5 mm

Technical description

Shank square □	24 mm
Thread depth	95.25 mm
Overall length L	200 mm
Tool material	HSS E
Thread Ø	38.1 mm
Tapping hole Ø	36.5 mm
Threads per inch	14

Number of clamping slots	4
Thread pitch	1.814 mm
Standard	DIN 376
Shank $\varnothing D_s$	32 mm
Number of cutting edges Z	4
Thread type	UNS
Thread size	1.1/2-14 UNS
Coating	TiN
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2xD for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap