

Garant**Left-hand thread blind hole machine tap, uncoated, Type: 7/8-14****Order data**

Order number	130041 7/8-14
GTIN	4062406046491
Item class	10N

Description**Note:**

Delivery time: 35 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UNF-LH

Tool material: HSS E

Standard: DIN 376

Threads per inch: 14

Thread \varnothing : 22.225 mm

Overall length L: 140 mm

Shank \varnothing D_s: 18 mm

Shank square \square : 14.5 mm

Tapping hole \varnothing : 20.4 mm

Technical description

Tapping hole \varnothing	20.4 mm
Overall length L	140 mm
Shank square \square	14.5 mm
Thread \varnothing	22.225 mm
Thread depth	55.56 mm
Tool material	HSS E
Number of cutting edges Z	4

Standard	DIN 376
Threads per inch	14
Shank $\varnothing D_s$	18 mm
Thread pitch	1.814 mm
Number of clamping slots	4
Thread type	UNF-LH
Thread size	7/8-14 UNF LH
Coating	uncoated
Flank angle	60°
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2xD for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap