

Garant**Left-hand thread through hole machine tap, TiN, Type: 11/16-16****Order data**

| | |
|--------------|-----------------|
| Order number | 130036 11/16-16 |
| GTIN | 4062406041830 |
| Item class | 10N |

Description**Note:**

Delivery time: 49 calendar days

Minimum order quantity: 2 pcs.

Special / custom-made product - return not possible

Thread type: UN-LH

Tool material: HSS E

Standard: DIN 376

Threads per inch: 16

Thread \varnothing : 17.462 mm

Overall length L: 125 mm

Shank \varnothing D_s: 14 mmShank square \square : 11 mmTapping hole \varnothing : 16 mm**Technical description**

| | |
|------------------------------------|----------|
| Tapping hole \varnothing | 16 mm |
| Number of cutting edges Z | 3 |
| Shank \varnothing D _s | 14 mm |
| Shank square \square | 11 mm |
| Tool material | HSS E |
| Overall length L | 125 mm |
| Thread depth | 34.92 mm |

| | |
|----------------------------------|--|
| Thread Ø | 17.462 mm |
| Number of clamping slots | 3 |
| Standard | DIN 376 |
| Threads per inch | 16 |
| Thread pitch | 1.588 mm |
| Thread type | UN-LH |
| Thread size | 11/16-16 UN LH |
| Coating | TiN |
| Flank angle | 60 ° |
| Thread standard | ASME B1.1 |
| Tolerance class | 1B |
| Tolerance class | 2B +0.20 |
| Tolerance class | 2B +0.10 |
| Tolerance class | 3B |
| Tolerance class | 2B |
| Tolerance class | 2B +0.05 |
| Taper lead form | B |
| Shank | Plain shank with h9 |
| Through-coolant | no |
| Application for type of drilling | up to 3×D for through holes |
| Cutting direction | left-hand |
| Type of threading tool | Machine tap for conventional machining |
| Colour ring | without |
| Type of product | Tap |