

Garant
Left-hand thread through hole machine tap, TiN, Type: 7/8-18

Order data

Order number	130036 7/8-18
GTIN	4062406041991
Item class	10N

Description
Note:

Delivery time: 49 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UNS-LH

Tool material: HSS E

Standard: DIN 376

Threads per inch: 18

Thread \varnothing : 22.23 mm

Overall length L: 140 mm

Shank \varnothing D_s: 18 mm

Shank square \square : 14.5 mm

Tapping hole \varnothing : 21 mm

Technical description

Number of cutting edges Z	3
Tool material	HSS E
Overall length L	140 mm
Number of clamping slots	3
Shank \varnothing D _s	18 mm
Threads per inch	18
Shank square \square	14.5 mm

Thread depth	66.69 mm
Tapping hole Ø	21 mm
Thread pitch	1.411 mm
Thread Ø	22.23 mm
Standard	DIN 376
Thread type	UNS-LH
Thread size	7/8-18 UNS LH
Coating	TiN
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap