

**Garant**
**Left-hand thread through hole machine tap, TiN, Type: 1.7/8-14**

**Order data**

Order number	130036 1.7/8-14
GTIN	4062406043049
Item class	10N

**Description**
**Note:**

Delivery time: 49 calendar days  
 Minimum order quantity: 1 pc.  
 Special / custom-made product - return not possible  
 Thread type: UNS-LH  
 Tool material: HSS E  
 Standard: DIN 376  
 Threads per inch: 14  
 Thread  $\varnothing$ : 47.625 mm  
 Overall length L: 250 mm  
 Shank  $\varnothing$  D<sub>s</sub>: 36 mm  
 Shank square □: 29 mm  
 Tapping hole  $\varnothing$ : 46 mm

**Technical description**

Tool material	HSS E
Number of clamping slots	4
Thread $\varnothing$	47.625 mm
Shank $\varnothing$ D <sub>s</sub>	36 mm
Standard	DIN 376
Number of cutting edges Z	4
Overall length L	250 mm
Threads per inch	14

Shank square □	29 mm
Thread depth	95.25 mm
Thread pitch	1.814 mm
Tapping hole Ø	46 mm
Thread type	UNS-LH
Thread size	1.7/8-14 UNS LH
Coating	TiN
Flank angle	60°
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap