

Garant
Left-hand thread through hole machine tap, TiN, Type: 11/16-20

Order data

Order number	130036 11/16-20
GTIN	4062406041823
Item class	10N

Description
Note:

Delivery time: 49 calendar days
 Minimum order quantity: 2 pcs.
 Special / custom-made product - return not possible
 Thread type: UN-LH
 Tool material: HSS E
 Standard: DIN 376
 Threads per inch: 20
 Thread \varnothing : 17.462 mm
 Overall length L: 125 mm
 Shank \varnothing D_s: 14 mm
 Shank square \square : 11 mm
 Tapping hole \varnothing : 16.25 mm

Technical description

Standard	DIN 376
Thread pitch	1.27 mm
Number of cutting edges Z	3
Shank \varnothing D _s	14 mm
Tool material	HSS E
Shank square \square	11 mm
Thread depth	34.92 mm

Number of clamping slots	3
Threads per inch	20
Thread Ø	17.462 mm
Overall length L	125 mm
Tapping hole Ø	16.25 mm
Thread type	UN-LH
Thread size	11/16-20 UN LH
Coating	TiN
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap