

Garant**Left-hand thread through hole machine tap, TiN, Type: 3/8-36****Order data**

Order number	130036 3/8-36
GTIN	4062406041427
Item class	10N

Description**Note:**

Delivery time: 49 calendar days

Minimum order quantity: 3 pcs.

Special / custom-made product - return not possible

Thread type: UNS-LH

Tool material: HSS E

Standard: DIN 371

Threads per inch: 36

Thread \varnothing : 9.525 mm

Overall length L: 100 mm

Shank \varnothing D_s: 10 mmShank square \square : 8 mmTapping hole \varnothing : 8.9 mm**Technical description**

Thread \varnothing	9.525 mm
Shank square \square	8 mm
Shank \varnothing D _s	10 mm
Standard	DIN 371
Threads per inch	36
Overall length L	100 mm
Tapping hole \varnothing	8.9 mm

Thread pitch	0.706 mm
Number of cutting edges Z	3
Tool material	HSS E
Number of clamping slots	3
Thread depth	28.59 mm
Thread type	UNS-LH
Thread size	3/8-36 UNS LH
Coating	TiN
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap