



## Laser distance meter DISTO™, Type: D2



### Order data

|              |               |
|--------------|---------------|
| Order number | 465550 D2     |
| GTIN         | 7640110696347 |
| Item class   | 47C           |

### Description

#### Version:

Impact resistant plastic casing with easy-to-use keypad with symbols. High quality **Leica glass lens** in an particularly temperature-resistant and sturdy **magnesium casing**. Illuminated and rotating colour display for optimum legibility. Power Range Technologie™ for measurements **up to 150 m without target board**. Laser class 2 tested in accordance with ISO 16331-1. Small and handy laser distance measuring tool, especially for indoor work.

#### Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

#### Supplied with:

Protective holder and wrist strap. Supplied with 2 batteries No. 081561 size LR3.

#### Note:

Data transfer via Bluetooth® Smart; also by smartphone using a Leica "DISTO™ Plan" app (Android from version 4.3, Apple from iPhone 4s). Easy generation of sketches.

### Technical description

|        |       |
|--------|-------|
| Weight | 100 g |
|--------|-------|

|   |                     |
|---|---------------------|
| indirect measurements (Pythagoras)                      | yes                 |
| Length  | 116 mm              |
| Height  | 26 mm               |
| IP Index of Protection                                  | IP 54               |
| Range   | 100 m               |
| Addition/subtraction                                    | yes                 |
| Recall last measurements                                | yes                 |
| Minimum / maximum measurements                          | yes                 |
| Width   | 44 mm               |
| Surface and volume calculations                         | yes                 |
| Power supply  | 081561 LR3          |
| Interface   | Bluetooth interface |
| multi-function endpiece                                 | yes                 |
| Measuring accuracy                                      | ±1.5 mm             |
| Article no of the battery / rechargeable battery fitted | 081561 LR3          |
| Number of batteries contained                           | 2                   |
| Series  | DISTO™              |
| Power supply  | Battery-powered     |
| Reversible reading                                      | mm / inch           |
| Laser class to IEC 825–1                                | 2                   |
| Type of product   | Distance meter      |

## Accessories

|   |            |
|---|------------|
| Alkaline-manganese batteries International size LR3 | 081561 LR3 |
|---|------------|